




ULTRASONIC FOBGING UNIT

HEUFT *exciter*



The HEUFT *exciter* ultrasonic fobbing unit

a leakage check for PET and glass bottles



FUNCTIONS

- generation of ultrasonic oscillations using a specially developed generator
- transfer of the oscillations to the bottle by means of an oscillating metal rail

- sprinkling jets to optimise the transfer of the oscillations to the bottle
- adjustable oscillation amplitude for a brand change
[\[more\]](#)*

THE ADVANTAGES

- low-friction and almost abrasion-free oscillating rail

- prevents contents which may be bad from endangering the health of the consumer
- cases or complete pallets are not soiled by leaking products
- the fast build-up of pressure in a plastic bottle stabilises the bottle and improves its transport characteristics and ability to be labelled
- water bath not required for transferring the oscillations

- the containers slide along the guide rails without impact pressure
[\[more\]](#)*

* [\[more\]](http://www.heuft.com/ec) detailed information on www.heuft.com/ec

